ebuildingproducts.com

SUBMITTAL: 1900 SERIES OLYMPUS AED & OXYGEN CABINET

Description: 1900 Series is designed to accommodate most AED's on the market today with room for an oxygen tank. Recessed models are ADAC-Compliant. Select from steel, stainless steel or aluminum construction.

Trim Construction: CRS with white powder-coat finish, #4 brushed stainless steel or clear anodized aluminum. 1-3/4" trim on face. Door: Formed door with 1-3/4" trim, mounted in a 5/8" door stop with zinc-plated handle and roller catch and continuous hinge. All models feature a clear acrylic window with graphics enclosed, zinc-plated handle and roller catch. Theft-deterrent SAF-T-LOK[™] available as option. Trim Style & Depth: *Recessed* – 3/8" flat trim, *Semi*-Recessed – 1½" square edge or 3" or 2½ rolled edge. *Surface-mount* has a square edge. Alarm: 85 db Commander (audible) alarm standard. Tub: White powder-coated CRS. Fire-rated available - See Separate Submittal

Oxygen: Accommodates up to "D" size cylinder. See options below.

Fire-Rated Option: Yes - See separate submittal.

STEP 1: SELECT MODEL NUMBER AND QUANTITY ON CHART (refer to chart on page 2)

A. Determine Trim Style according to wall depth. B. Determine Tub I.D. according to size most suited for extinguisher and wall opening.

STEP 2: SELECT DOOR STYLE Check one box below

 F12
 Full Acrylic Glazing; Pull & AED Graphics
 E17
 Horizontal Dual Panel; Tempered, SAF-T-LOK[™], Pull & AED Decal

 F17
 Full Tempered Glazing; Pull & AED Decal
 S21
 Solid Door; Pull & AED Decal

 G12
 Full Glazing; Acrylic, SAF-T-LOK[™], Pull & AED Graphics
 L22
 Solid; SAF-T-LOK[™], Pull & AED Decal

 G17
 Full Glazing; Tempered, SAF-T-LOK[™], Pull & AED Decal
 V12
 Vertical Duo; Acrylic Glazing, Pull & AED Decal D12

 Horizontal Duo Panel; Acrylic, Pull & AED Decal
 V17
 Vertical Duo; Tempered Glass, Pull & AED Decal D17


 Horizontal Duo Panel; Tempered, Pull & AED Decal
 W12
 Vertical Duo; Acrylic, SAF-T-LOK[™], Pull & AED Decal


 E12
 Horizontal Dual Panel; Acrylic, SAF-T-LOK[™], Pull & AED Decal
 W12
 Vertical Duo; Acrylic, SAF-T-LOK[™], Pull & AED Decal

 E12
 Horizontal Dual Panel; Acrylic, SAF-T-LOK[™], Pull & AED Decal
 W17
 Vertical Duo; Tempered, SAF-T-LOK[™], Pull & AED Decal

Optional Features at Additional Cost:

(SA) <u>Siren Strobe Alarm</u> and 85 db Alarm (3" Trim & Surface-Mount Models Only)		LIF-O-GEN® Oxygen System that features easy-to-use automatic flow system.
(STC) Saf-T-Clasp for Visual Notification When Door has been opened		(14MAG) Magnetic Door Contact for Existing Alarm
Systems Custom Door Graphics available—company logos, photos, etc. Contact C	S.	(14RR) Roller Reed Ball Contact for Existing Alarm Systems
AED Wall Signs <u>14S</u> 14TX <u>14XS - See Separate Submittal</u>		Custom Colors (Provide Paint Chip) Contact Customer Service
Optional Colors View Optional Colors Online Contact Customer Service		Optional Tub Color:BlackRed
Optional Anodized Aluminum Finishes View Finishes Online		Optional Tub MaterialStainlessAluminum
Bronze or Brass Finish Contact Customer Service		Etched or Engraved Lettering in Glass or Metal More Info.
(Pulls painted to match finish of color anodized, brass or bronze cabinets)		Recessed Pull, Pulls in Other Finishes, Lever Handle
Optional Stainless Steel Finishes View Finishes Online		









1915F12 Cabinet with 3/8" Flat Trim

ebuildingproducts.com

SUBMITTAL: 1900 SERIES OLYMPUS AED & OXYGEN CABINET

PAGE 2 OF 2





TRIM & DOOR MATERIAL & SERIES #							TUB I.D.			FRAME O.D.		WALL OPENING NON RATED		
QTY	STEEL	QTY	ALUMINUM	QTY	STAINLESS STEEL	TRIM STYLE	АВС			E F		W H D		
	1915		1925		1935	3/8″ Flat Trim	18″	18″	8″	21-3/8″	21-3/8″	19″	19″	8″
	1916		1926		1936	1-1/2" Square	18″	18″	8″	21-3/8″	21-3/8″	19″	19″	6-7/8″
	1917		*1927		1937	3" Rolled (1927 is 2-1/2")	18″	18″	8″	21-3/8″	21-3/8″	19″	19″	*5-3/4″
	1913		1923		1939	Surface Mount Sq. Trim	21-3/16″	21-3/16"	8-1/2″	21-3/8″	21-3/8″			

* Model 1927 has 2-1/2" Trim & Requires 5/8" Deeper Wall Opening